


# PHILIPS

## Maxos Fusion

### LL500T Gen2



50Hz  
60Hz

220V  
240V



LEDs






IP20  
LL500T

IK02




|             | L(mm) | 7P<br>kg | 9P<br>kg | 13P<br>kg |
|-------------|-------|----------|----------|-----------|
| LL512T Gen2 | 1138  | 1.7      | 1.7      | 1.7       |
| LL523T Gen2 | 2276  | 3.3      | 3.3      | 3.3       |
| LL546T Gen2 | 4552  | 6.4      | 6.4      | 6.4       |



N L1 L2 L3 - 2,5mm<sup>2</sup>  
 4 5 6 7 8 9 10 11 - 1,5mm<sup>2</sup>

Use 1,5mm<sup>2</sup> for DA / EL



Max. 230V/10A allowed on 1,5mm<sup>2</sup>





442710470530




2023-03-03  
 © Signify Holding  
 All rights reserved


Printed in Poland  
 Data subject to change without notice  
 Keep for future reference: [www.philips.com/lighting](http://www.philips.com/lighting)




LL500Z PB







### Suspension brackets



| Pos. | Description            |   |
|------|------------------------|---|
| 1    | LL500Z SMB WH          | Surface mounted bracket white                             |
|      | LL500Z SMB SI          | Surface mounted bracket silver                            |
|      | LL500Z SMB BK          | Surface mounted bracket black                             |
| 2    | LL500Z MB-SW WH        | Mounting bracket for suspension wire (2 mm), white        |
|      | LL500Z MB-SW SI        | Mounting bracket for suspension wire (2 mm), silver       |
|      | LL500Z MB-SW BK        | Mounting bracket for suspension wire (2 mm), black        |
| 3    | LL500Z MB-SW2 L5000 WH | Mounting bracket with suspension wire l = 5000 mm, white  |
|      | LL500Z MB-SW2 L5000 SI | Mounting bracket with suspension wire l = 5000 mm, silver |
|      | LL500Z MB-SW2 L5000 BK | Mounting bracket with suspension wire l = 5000 mm, black  |
| 4    | LL500Z CB-CH WH        | Chain bracket, white                                      |
|      | LL500Z CB-CH SI        | Chain bracket, silver                                     |
|      | LL500Z CB-CH BK        | Chain bracket, black                                      |
| 5    | LL500Z PB WH           | profile bracket for visible T-profiles, white             |
|      | LL500Z PB SI           | profile bracket for visible T-profiles, silver            |
|      | LL500Z PB BK           | profile bracket for visible T-profiles, black             |
| 6    | LL500Z SW2 L1250       | suspension wire diameter 2 mm, L=1250mm                   |
|      | LL500Z SW2 L3000       | suspension wire diameter 2 mm, L=3000mm                   |
|      | LL500Z SW2 L5000       | suspension wire diameter 2 mm, L=5000mm                   |

© 2021 Signify Holding

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Signify Holding  
The Netherlands